


DATA SHEET

CoaXPRESS CXP-6 Interface Cable

4 BNC to 4 DIN 1.0/2.3 screw lock, 5.0 m

Order code:
13034

V1.0.0
2018-June-07




Connector 1
4 BNC

Cable
Four Bundle

Connector 2
4 DIN 1.0/2.3 Screw lock

Cable label



Specifications

| Feature | Specification |
|-----------------------|------------------|
| Length | 5.0 m ± 100 mm |
| Diameter | 13.64 mm |
| Bandwidth | 4.5 GHz |
| Static bending radius | 136 mm |
| Outer Jacket | TPE |
| Temperature range | -30 °C to +75 °C |
| Regulations | RoHS |