


DATA SHEET

Order code:
9433

Interface cable


USB 3.0 Micro-B screw lock
to Type A screw lock, 3.0 m

V1.0.0
2016-Sep-12



Connector 1

USB 3.0 Micro-B male connector
with screw lock




Cable

Note


Unit in technical drawings is [mm].

Connector 2


USB 3.0 Type A male connector
with screw lock




Screw detail



Wiring diagram



Screw detail



Specifications

Feature	Specification
Length	3.0 m ± 30 mm
Diameter	5.5 mm
Classification	Industrial suitability for static applications
Static bending radius	≥ 55 mm
Dynamic bending radius	For static applications only
Temperature range	-20 °C to +80 °C
Regulations	UL2725, RoHS 2011/65/EU, REACH