


DATA SHEET


Interface cable

 USB 3.0 Micro-B screw lock
to Type A screw lock, 8.0 m

 Order code:
9435

 V1.0.0
2016-Sep-12


Connector 1


 USB 3.0 Micro-B male connector
with screw lock


Cable


Note

Unit in technical drawings is [mm].


Connector 2

 USB 3.0 Type A male connector
with screw lock



Screw detail



Wiring diagram



Screw detail


Specifications

Feature	Specification
Length	8.0 m ± 80 mm
Diameter	5.5 mm
Classification	Industrial suitability for static applications
Static bending radius	≥ 55 mm
Dynamic bending radius	For static applications only
Temperature range	-20 °C to +80 °C
Regulations	UL2725, RoHS 2011/65/EU, REACH