

DATA SHEET

I/O cable

Hirose 6-pin female to open end, 2.0 m

Order code:


9436

V1.0.0

2016-Sep-28

Compatible camera family

Mako U





Connector 1

HR10A-7P-6S(73) connector


Cable

Connector 2


Open end: shield and wire
tinned and soldered



Cable label



Wiring diagram



Notes

Unit in technical drawings is [mm].

All shielded pairs connect to shield wire.

Specifications

Feature	Specification
Length	2.0 m ± 50 mm
Diameter	4.9 mm
Classification	Industrial suitability for static applications
Static bending radius	29.4 mm
Dynamic bending radius	For static applications only
Temperature range	On request
Compliance	UL20276, RoHS 2011/65/EU, REACH