


DATA SHEET

Interface cable

IEEE 1394a 6-pin to IEEE 1394a 6-pin, 2.0 m


Order code:
K1200063

V1.0.0
2016-Sep-28



Connector 1


IEEE 1394a 6-pin molded connector




Cable

Connector 2


IEEE 1394a 6-pin molded connector



Cable label



Wiring diagram



Note

Unit in technical drawings is [mm].

Specifications

| Feature | Specification |
|------------------------|--|
| Length | 2.0 m ± 100 mm |
| Diameter | 5.7 mm |
| Classification | Industrial Suitability for static applications |
| Static bending radius | 34.2 mm |
| Dynamic bending radius | For static applications only |
| Temperature range | On request |
| Regulations | UL20276, RoHS 2011/65/EU, REACH |