


DATA SHEET

## Interface cable

IEEE 1394a 6-pin to IEEE 1394a 6-pin, 0.5 m


Order code:  
K1200071

V1.0.0  
2016-Sep-28



### Connector 1


IEEE 1394a 6-pin molded connector




### Cable

### Connector 2


IEEE 1394a 6-pin molded connector



### Cable label



### Wiring diagram



### Note

Unit in technical drawings is [mm].

### Specifications

Feature	Specification
Length	0.5 m ± 10 mm
Diameter	5.7 mm
Classification	Industrial Suitability for static applications
Static bending radius	34.2 mm
Dynamic bending radius	For static applications only
Temperature range	On request
Regulations	UL20276, RoHS 2011/65/EU, REACH