


DATA SHEET

Order code:  
K1200112


## Interface cable

IEEE 1394b 9-pin screw lock  
to IEEE 1394b 9-pin screw lock, 1.0 m


V1.0.0  
2016-Sep-28




**Connector 1**  
IEEE 1394b 9-pin molded  
connector with screw lock




**Connector 2**  
IEEE 1394b 9-pin molded  
connector with screw lock



Cable label



Wiring diagram



Note

Unit in technical drawings is [mm].

Specifications

Feature	Specification
Length	1.0 m ± 50 mm
Diameter	7.2 mm
Classification	Industrial suitability for static applications
Static bending radius	43.2 mm
Dynamic bending radius	For static applications only
Temperature range	On request
Regulations	UL20276, RoHS 2011/65/EU, REACH