



## DATA SHEET

**Interface cable**


 IEEE 1394b 9-pin screw lock  
to IEEE 1394a 6-pin latch, 4.5 m


 Order code:  
K1200171

 V1.0.0  
2016-Sep-28

**Connector 1**



 IEEE 1394b 9-pin connector with  
die cast shell, screw lock


Mating Face View


**Cable**
**Connector 2**

 IEEE 1394a 6-pin connector  
with latch


Mating Face View

**Cable label**

**Wiring diagram**

**Note**

Unit in technical drawings is [mm].

**Specifications**

Feature	Specification
Length	4.5 m ± 50 mm
Diameter	7.2 mm
Classification	Industrial suitability for static applications
Static bending radius	43.2mm
Dynamic bending radius	For static applications only
Temperature range	On request
Regulations	UL20276, RoHS 2011/65/EU, REACH