


DATA SHEET

Interface cable

IEEE 1394a 6-pin to IEEE 1394a 6-pin, 1.0 m


Order code:
K1200226

V1.0.0
2016-Sep-28



Connector 1


IEEE 1394a 6-pin molded connector




Cable

Connector 2


IEEE 1394a 6-pin molded connector



Cable label



Wiring diagram



Note

Unit in technical drawings is [mm].

Specifications

Feature	Specification
Length	1.0 m ± 100 mm
Diameter	5.7 mm
Classification	Industrial Suitability for static applications
Static bending radius	34.2 mm
Dynamic bending radius	For static applications only
Temperature range	On request
Regulations	UL20276, RoHS 2011/65/EU, REACH