


DATA SHEET

## Interface cable

IEEE 1394b 9-pin screw lock  
to IEEE 1394a 6-pin standard, 4.5 m


Order code:  
K1200288

V1.0.0  
2016-Sep-28




### Connector 1

IEEE 1394b 9-pin connector with  
die cast shell, screw lock




Mating Face View



### Cable


### Connector 2

IEEE 1394a 6-pin connector




Mating Face View

### Cable label



### Wiring diagram



### Note

Unit in technical drawings is [mm].

### Specifications

| Feature                | Specification                                  |
|------------------------|--|
| Length                 | 4.5 m ± 100 mm                                 |
| Diameter               | 4.8 mm   |
| Classification         | Industrial suitability for static applications |
| Static bending radius  | 28.8 mm  |
| Dynamic bending radius | For static applications only                   |
| Temperature range      | On request                                     |
| Compliance             | UL20276, RoHS 2011/65/EU, REACH                |