


DATA SHEET

Order code:
K1200306

Interface cable



IEEE 1394b 9-pin screw lock
to IEEE 1394b 9-pin screw lock, 0.5 m

V1.0.0
2016-Sep-28




IEEE 1394b 9-pin molded
connector with screw lock


IEEE 1394b 9-pin molded
connector with screw lock



Cable label



Wiring diagram



Note

Unit in technical drawings is [mm].

Specifications

| Feature | Specification |
|------------------------|--|
| Length | 0.5 m ± 10 mm |
| Diameter | 7.2 mm |
| Classification | Industrial suitability for static applications |
| Static bending radius | 43.2 mm |
| Dynamic bending radius | For static applications only |
| Temperature range | On request |
| Regulations | UL20276, RoHS 2011/65/EU, REACH |