


DATA SHEET

Order code:
K13079

Interface cable


IEEE 1394b 9-pin screw lock
to IEEE 1394b 9-pin screw lock, 5.0 m

V1.0.0
2018-Jul-06




Connector 1

IEEE 1394b 9-pin molded
connector with screw lock




Cable

See Cable label




Connector 2


IEEE 1394b 9-pin molded
connector with screw lock



Cable label



Wiring diagram



Note

Unit in technical drawings is [mm].

Specifications

Feature	Specification
Length	5.0 m ± 100 mm
Diameter	7.2 mm
Classification	Industrial suitability for static applications
Static bending radius	≥ 72.0 mm
Dynamic bending radius	For static applications only
Temperature range	-20 °C to +80 °C
Regulations	Cable material: UL2725 Cable jacket and connectors: UL94V0 RoHS