




DATA SHEET




Interface cable

 IEEE 1394b 9-pin screw lock
 to IEEE 1394b 9-pin screw lock, 10.0 m

 Order code:
 K13080

 V1.0.0
 2018-Jul-06

Connector 1

 IEEE 1394b 9-pin molded
 connector with screw lock

Cable

Connector 2

 IEEE 1394b 9-pin molded
 connector with screw lock

Cable label

Wiring diagram

Note

Unit in technical drawings is [mm].

Specifications

Feature	Specification
Length	10.0 m ± 100 mm
Diameter	7.2 mm
Classification	Industrial suitability for static applications
Static bending radius	≥ 72.0 mm
Dynamic bending radius	For static applications only
Temperature range	-20 °C to +80 °C
Regulations	Cable material: UL2725 Cable jacket and connectors: UL94V0 RoHS