

Mako G

G-125



- Ultra-compact design
- Affordable
- Power over Ethernet
- 30 fps @ full resolution

基本描述

GigE camera with Sony ICX445 CCD sensor, 30.3 fps

Mako G-125 is a 1.2 megapixel GigE machine vision camera that incorporates the high quality Type 1/3 (6.0 diagonal) Sony ICX445 CCD sensor with EXview HAD technology. At full resolution, this camera runs 30.3 frames per second. With a smaller region of interest, higher frame rates are possible. Mako G-125 is offered in both monochrome (G-125B) and color (G-125C) models.

Mako G cameras have the same ultra-compact form factor and the same mounting positions as many analog cameras. All models include Power over Ethernet (PoE), three opto-isolated outputs, and a 64 MByte image buffer. The image quality profits from the precisely aligned sensor. By default monochrome models ship with no optical filter and color models ship with IRC Hoya C-5000 IR cut filter.

Options:

- Various optical filter and lens mount options
- White medical housing


See the [Modular Concept](#) for lens mount, optical filter, and housing design options. See the [Customization and OEM Solutions](#) page for additional options.

性能参数

Mako G	G-125
接口	IEEE 802.3 1000BASE-T, IEEE 802.3af (PoE)



Mako G	G-125
分辨率	1292 (H) × 964 (V)
传感器	Sony ICX445
传感器类型	CCD Progressive
传感器尺寸	Type 1/3
像元尺寸	3.75 μm × 3.75 μm
标准镜头接口	C-Mount
最大满帧帧率	30.3 fps
ADC	14 bit
缓存 (RAM)	64 MByte
非易失性内存 (Flash)	1024 KByte (for selected models only)
输出	
Bit位数	8/12 bit
黑白像素格式	Mono8, Mono12, Mono12Packed
YUV彩色像素格式	YUV411Packed, YUV422Packed, YUV444Packed
RGB彩色像素格式	RGB8Packed, BGR8Packed
原始像素格式	BayerRG8, BayerRG12, BayerRG12Packed
通用输入输出(GPIOs)	
光耦 I/Os	1 input, 3 outputs
工作条件/尺寸	
工作温度	+5 °C to +45 °C housing temperature
电源要求 (DC)	12 to 24 VDC; PoE
功耗	2.3 W at 12 VDC; 2.7 W PoE
重量	80 g
尺寸(L × W × H in mm)	60.5 × 29.2 × 29.2 (incl. connectors)
符合规范	CE: 2014/30/EU (EMC), 2011/65/EU, including amendment 2015/863/EU (RoHS); FCC Class B; CAN ICES-003



特性

Image optimization features:

- Auto gain (manual gain control: 0 to 30 dB; 1 dB increments)
- Auto exposure (manual exposure control: 12 μ s to 84 s; 1 μ s increments)
- Auto white balance (G-125C only)
- Binning
- Color correction, hue, saturation (G-125C only)
- Gamma correction
- One look-up table (LUT)
- Region of interest (ROI), separate ROI for auto features

Camera control features:

- Event channel
- Image chunk data
- Storable user sets
- StreamBytesPerSecond (easy bandwidth control)
- Stream hold
- Sync out modes: Trigger ready, input, exposing, readout, imaging, strobe, GPO
- Temperature monitoring (main board only)
- Non-volatile memory 1024 KByte (for selected models only)

外形尺寸





应用场景

Mako G-125 is ideal for a wide range of applications including:

- Robotics
- Quality control
- Inspection, surveillance
- Industrial imaging
- Machine vision
- Logistics