


# Prosilica GT 1660



- Versatile temperature range for extreme environments
- PTP
- PoE
- P-Iris and DC-Iris lens control

## 基本描述

### 1.9 Megapixel machine vision camera for extreme environments

Prosilica GT1660 is a 1.9 Megapixel camera with a GigE Vision compliant Gigabit Ethernet port and Hirose I/O port. Prosilica GT1660 is offered in both monochrome and color models. This camera incorporates the high-quality ON Semiconductor KAI-02050 TRUESENSE CCD sensor providing excellent monochrome and color image quality. At full resolution, this camera runs 62.1 frames per second. With a smaller region of interest, higher frame rates are possible. It is a rugged camera designed to operate in extreme environments and fluctuating lighting conditions. This camera offers Precise iris lens control allowing users to fix the aperture size to optimize depth of field, exposure, and gain without the need for additional control elements. By default monochrome models ship with no optical filter and color models ship with an IRC30 IR cut filter.

#### Benefits and features:

- Monochrome (GT1660) and color (GT1660C) models
- GigE Vision interface with Power over Ethernet
- Screw mount RJ45 Ethernet connector for secure operation in industrial environments
- Supports cable lengths up to 100 meters (CAT-5e or CAT-6)
- Trigger over Ethernet (ToE) Action Commands allow for a single cable solution to reduce system costs
- Comprehensive I/O functionality for simplified system integration
- Popular C-Mount lens mount
- Easy camera mounting via standard M3 threads or optional tripod adapter
- Easy software integration with Allied Vision's [Vimba SDK](#) and compatibility to the most popular [third party image-processing libraries](#).

## Options:

- Available with CS-Mount, F-Mount, EF-Mount Birger, M42-Mount
- Available with IR cut filter or protection glass

See the [Modular Concept](#) for lens mount and optical filters options. See the [Customization and OEM Solutions](#) page for additional options.


## 性能参数

|                     |  |
|---------------------|--|
| Prosilica GT        | 1660   |
| 接口                  | IEEE 802.3 1000BASE-T, IEEE 802.3af (PoE)        |
| 分辨率                 | 1600 (H) × 1200 (V)                              |
| 传感器                 | ON Semi KAI-02050                                |
| 传感器类型               | CCD Progressive                                  |
| 传感器尺寸               | Type 2/3   |
| 像元尺寸                | 5.5 μm × 5.5 μm                                  |
| 标准镜头接口              | C-Mount  |
| 最大满帧帧率              | 62.1 fps   |
| ADC                 | 14 bit   |
| 缓存 (RAM)            | 128 MByte  |
| 非易失性内存 (Flash)      | 1024 KByte (for selected models only)            |
| 输出                  |  |
| Bit位数               | 14 (mono) - 12 (color) bit                       |
| 黑白像素格式              | Mono8, Mono12, Mono12Packed, Mono14              |
| YUV彩色像素格式           | YUV411Packed, YUV422Packed, YUV444Packed         |
| RGB彩色像素格式           | RGB8Packed, BGR8Packed, RGBA8Packed, BGRA8Packed |
| 原始像素格式              | BayerGR8, BayerGR12, BayerRG12Packed             |
| 通用输入输出(GPIOs)       |  |
| TTL I/Os            | 1 input, 2 outputs                               |
| 光耦 I/Os             | 1 input, 2 outputs                               |
| RS232               | 1  |
| 工作条件/尺寸             |  |
| 工作温度                | -20 °C to +60 °C ambient (without condensation)  |
| 电源要求 (DC)           | 7 to 25 VDC; PoE                                 |
| 功耗                  | 5.1 W at 12 VDC; 6.3 W PoE                       |
| 重量                  | 224 g  |
| 尺寸(L × W × H in mm) | 92 × 53.3 × 33 (including connectors)            |

Prosilica GT  
符合规范

1660

CE: 2014/30/EU (EMC), 2011/65/EU, including amendment 2015/863/EU (RoHS); FCC Class A; CAN ICES-003 Issue 4/5



## 特性

### Image optimization features:

- Auto gain (manual gain control: 0 to 32 dB)
- Auto exposure (manual exposure control: 10  $\mu$ s to 26.8 s)
- Auto white balance (GT1660C only)
- Binning (horizontal and vertical)
- Color correction, hue, saturation (GT1660C only)
- Column defect masking
- Decimation X/Y
- Gamma correction
- Three look-up tables (LUTs)
- Region of interest (ROI), separate ROI for auto features
- Reverse X/Y






### Camera control features:

- P-Iris and DC-Iris lens control



- Event channel
- Image chunk data
- IEEE 1588 Precision Time Protocol (PTP)
- RS232
- Storable user sets
- StreamBytesPerSecond (bandwidth control)
- Stream hold
- Sync out modes: Trigger ready, input, exposing, readout, imaging, strobe, GPO
- Tap mode switchable in Vimba Viewer 2.0 or later (four-tap, one-tap)
- Temperature monitoring (main board and sensor board)
- Trigger over Ethernet (ToE) Action Commands
- Non-volatile memory 1024 KByte (for selected models only)

## 外形尺寸





## 应用场景

Prosilica GT1660 is ideal for a wide range of applications including:

- Outdoor imaging
- Traffic imaging and ITS
- Public security and surveillance
- Industrial inspection
- Machine vision
- Military and space applications