



# Goldeye

## CL-032 SWIR

- Goldeye CL-032 SWIR NIR camera with InGaAs sensor, 636 × 508 pixels, Peltier cooling

见所未见

### 搭载 InGaAs 传感器技术的短波红外 (SWIR) 相机

Goldeye CL-032 SWIR 搭载 InGaAs FPA 636 × 508 传感器，在 0.3 MP 分辨率下速度可达 30.0 帧/秒。

Goldeye 相机配备了 InGaAs 传感器技术，对 400-1700 nm 波段红外短波非常敏感。所有 Goldeye SWIR 相机都可以超高帧率运行，拍摄出无与伦比的低噪图像。此款相机是不可见光谱的工业和科技应用的完美选择。所有 Goldeye 机型均搭载 Camera Link 或 GigE Vision 接口。

The Goldeye is a short-wave infrared (SWIR) camera. It has a spectral response from 900 nm to 1700 nm. Its InGaAs sensors feature high sensitivity, very good linearity, and a high damage threshold against intense illumination. Thanks to the 14-bit processing and the numerous image correction features, Goldeye cameras produce an outstanding, low-noise image quality. The camera is also available with Peltier cooling. The Peltier cooling is beneficial especially for applications with long exposure times, or for exact temperature measurements.

- C-Mount, compatible with standard machine vision lenses
- GigE Vision, also available with Camera Link interface
- Options:
  - Peltier cooling for long exposure times and exact temperature measurements

### 性能参数

Goldeye CL-032 SWIR	
接口	Camera Link Base
分辨率	636 (H) × 508 (V)
传感器	InGaAs FPA 636 × 508

## Goldeye CL-032 SWIR

传感器类型	InGaAs
传感器尺寸	No standard size
像元尺寸	25 $\mu\text{m}$ $\times$ 25 $\mu\text{m}$
标准镜头接口	C-Mount, F-Mount
最大满帧帧率	30 fps


### 输出

通用输入输出 (GPIOs)

工作条件/尺寸

符合规范 CE: 2014/30/EU (EMC), 2011/65/EU (RoHS)

## 量子转换效率



## 特性

- Gain, up to factor 20 at short exposure times

- Exposure time 64  $\mu$ s to 1 s
- Shipped with built-in correction data sets
- Gain/offset correction (NUC / non-uniformity correction) for each pixel
- Bad pixel correction
- Background (FPN) correction
- Continuous mode (image acquisition with maximum frame rate)
- Image On Demand mode (triggered image acquisition)

In combination with Allied Vision's AcquireControl software, extensive image analysis functions are available:

- Pseudo color LUT with several color profiles
- Auto contrast
- Auto brightness
- Analyze multiple regions (rectangular, circle) within the image
- Real-time statistics and histogram display

## 应用场景

Goldeye NIR cameras are very sensitive in the NIR spectrum, show excellent linearity, and tolerate intense illumination. They are the perfect choice for numerous NIR applications:

- Near-infrared imaging
- Thermal imaging of hot objects (in a range of 250°C to 800°C)
- Imaging spectroscopy
- Laser beam profiling
- Sorting according to plastic
- Semiconductor inspection
- Water or moisture detection
- Medical science and biology
- Vision enhancement